

STYLEA

5925PJ040L51-10 LH 9011/9011/9011/7016

EAN 4031582359862



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	35 mm
Overall width	52 mm
Overall weight	0.06 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	12 mm
Swivel radius	45 mm
Swivel interference	90 mm
Dome diameter	15.2 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Anthracite grey (RAL7016)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	40 mm
Tread width	12 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	12 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

STYLEA

5925PJ1040L51-10 LH 9011/9011/9011/7016

EAN 4031582359862

Order number 00770014

Product Drawings



BETTER MOBILITY. BETTER LIFE.

