

NOVATECH

FTP 250X50-Ø30 HL60

EAN 4031582331059
Order number 00838765



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	1.97 in
Axle hole diameter	1.18 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3174.65 lb
Load capacity at 3.7 mph	2645.54 lb
Load capacity Static	5291.09 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	13.85 lb

TECHNICAL DRAWINGS

