

# AGILA

2470DIK150R07-Ø19-21,5

EAN 4031582328417



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	7.4 in
Overall weight	3.25 lb

## HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	1.77 in
Swivel radius	4.72 in
Swivel interference	9.45 in

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Hardness of tread (A)	80 Shore A

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.75 in
Expander fitting (Maximum)	0.85 in
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2470DIK150R07-Ø19-21,5

EAN 4031582328417



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

