

# STYLEA

5920XOI075B10-11X20 DOM20

EAN 4031582355208



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Load capacity at 1.8 mph	110.23 lb
Electric conductive	✓
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.19 in
Overall width	2.13 in

## WHEEL

Body material	Polyamide, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.31 in
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.44 in
Swivel interference	4.88 in
Dome diameter	0.79 in

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

PRODUCT INFORMATION

# STYLEA

5920XOI075B10-11X20 DOM20

EAN 4031582355208



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

