

LUMINA

A520POI042L51-8 CHROME/9011

EAN 4031582317268
Order number 00072826



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	49 mm
Overall width	38 mm
Overall weight	0.026 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	42 mm
Tread width	6 mm
Body width	6 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Offset	16 mm
Swivel radius	39 mm
Swivel interference	78 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	8 mm

PRODUCT INFORMATION

LUMINA

A520POI042L51-8 CHROME/9011

EAN 4031582317268
Order number 00072826



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

