

LINEA

5947XSP100P30-13 RAL9002 NC

EAN 4031582350579



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Linea |
| Housing type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 120 kg |
| Load capacity Static | 240 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 118 mm |
| Overall width | 82 mm |
| Overall weight | 0.724 kg |

WHEEL

| | |
|-----------------------|---|
| Body material | Polyamide, electric conductive |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 20 mm |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Offset | 32 mm |
| Swivel radius | 108 mm |
| Swivel interference | 216 mm |
| Dome diameter | 52 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |



LINEA



5947XSP100P30-13 RAL9002 NC

EAN 4031582350579



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award