

STORA

2875ZHP125P30-13 LEFT

EAN 4031582357691
Order number 00030376



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric conductive	✓
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	153 mm
Overall width	70 mm
Overall weight	0.844 kg

WHEEL

Body material	Flanged wheel
Tread material	Thermoplastic rubber, antistatic
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Special Function
Swivel bearing	Two ball races
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm
Dome diameter	65 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ADDITIONAL INFORMATION

Designed for the following palletsize: track width: approx. 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.

STORA

2875ZHP125P30-13 LEFT

EAN 4031582357691
Order number 00030376



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

