

LUMINA

5520UAI075L51-11 ~9006/~9006/9011

EAN 4031582310634
Order number 00074379



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Lumina |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 88 mm |
| Overall width | 65 mm |
| Overall weight | 0.28 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread color | Graphite black (RAL9011) |
| Wheel color | White aluminium (RAL9006) |
| Threadguards | Without threadguard |
| Diameter | 75 mm |
| Tread width | 10 mm |
| Axle hole diameter | 0 mm |
| Hub length | 0 mm |
| Body width | 10 mm |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|---------------------------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel bearing | Stem, swiveling |
| Colour | White aluminium (RAL9006) |
| Offset | 30 mm |
| Swivel radius | 73 mm |
| Swivel interference | 146 mm |
| Dome diameter | 45 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 11 mm |

PRODUCT INFORMATION

LUMINA

5520UAI075L51-11 ~9006/~9006/9011

EAN 4031582310634
Order number 00074379



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

