

# AGILA

2470PJP075P40

EAN 4031582010466  
Order number 00004471



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	100 mm
Overall width	43 mm
Overall weight	0.283 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	24 mm
Swivel radius	61.5 mm
Swivel interference	123 mm
Dome diameter	43 mm

## FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

# AGILA

2470PJP075P40

EAN 4031582010466  
Order number 00004471



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

