

# LUMINA

6A20POI050L51-8 ZAMAK/9011

EAN 4031582311327  
Order number 00073845



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	59 mm
Overall width	55 mm
Overall weight	0.094 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Offset	20 mm
Swivel radius	54 mm
Swivel interference	108 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	8 mm

PRODUCT INFORMATION

# LUMINA

6A20POI050L51-8 ZAMAK/9011

EAN 4031582311327  
Order number 00073845



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

