

KAPPA FLEX

9758ITP200P63 SH92A

EAN 4031582443646



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ● ○

CORE ATTRIBUTES

Product Name	Kappa flex
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	450 kg
Load capacity at 6 km/h	300 kg
Electric Conductive	No
Stainless	No
Load capacity Static	900 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	260 mm
Overall weight	4.7 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	With spring

WHEEL

Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	142 mm
Plate width	111 mm
Plate hole length (Minimum)	99 mm
Plate hole length (Maximum)	112 mm
Plate hole width (Minimum)	74 mm
Plate hole width (Maximum)	83 mm
Plate hole diameter	12.7 mm