

# DELTA TWIN

9948ITP125P63 SOFT CV

EAN 4031582365894  
Order number 00837761



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Delta twin
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1653.47 lb
Load capacity at 3.7 mph	1322.77 lb
Load capacity Static	3306.93 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	7.01 in
Overall width	6.18 in
Overall weight	8.5 lb

## WHEEL

Body material	Aluminum
	soft
	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Traffic gray A (RAL7042)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Color	Transparent coating
Dome diameter	5.35 in

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	5.39 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	4.13 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

# DELTA TWIN

9948ITP125P63 SOFT CV

EAN 4031582365894  
Order number 00837761



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

