

AGILA US

2675POO4X1.25P52-95X70

EAN 4031582435702



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila US
Housing type	Swivel castor with wheel brake
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	661.39 lb
Overall height	5.16 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	4 in
Tread width	1.25 in
Axle hole diameter	0.39 in
Hub length	1.61 in
Hardness of tread (D)	66 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	1.5 in
Swivel radius	4.65 in
Swivel interference	9.29 in

FITTING

Fitting type	Rectangular plate, US-bolt hole spacing
Plate length	3.74 in
Plate width	2.76 in
Plate hole length (Maximum)	1.75 in
Plate hole width (Maximum)	3 in
Plate hole diameter	0.43 in