

LINEA

5940USC125R05-32 9002 CC

EAN 4031582382792



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Linea
Type	Swivel castor
Standard	EN12531 - Hospital Bed Castors
Load capacity at 3 km/h	150 kg
Load capacity at 4 km/h	150 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	450 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	130 mm
Overall width	71 mm
Overall weight	0.93 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Precision ball bearing
Housing Color	Grey white (RAL9002)
Offset	40 mm
Swivel radius	108 mm
Swivel interference	216 mm
Dome diameter	45.5 mm
Hint	Housing with integrated cable catcher made of Polyethylene.

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, stainless
Wheel Color	Grey white (RAL9002)
Threadguards	With threadguard
Diameter	125 mm
Tread width	15 mm
Body width	15 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Solid stem, round
Bolt diameter	32 mm
Bolt length	45 mm
Bolt thread position	7 mm
Bolt mounting holes quantity	2



Deutscher
Designer
Club



Interzum
Award



IF Design
Award

LINEA

5940USC125R05-32 9002 CC

EAN 4031582382792

Order number 00061513

Product Drawings



BETTER MOBILITY. BETTER LIFE.

