

LINEA

5940UAP150R05-32 9002

EAN 4031582338898
Order number 00034522



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Linea |
| Housing type | Swivel castor |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 3 km/h | 150 kg |
| Load capacity at 4 km/h | 150 kg |
| Load capacity Static | 450 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 155 mm |
| Overall width | 71 mm |
| Overall weight | 1.087 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel color | Grey white (RAL9002) |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 15 mm |
| Body width | 15 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Colour | Grey white (RAL9002) |
| Offset | 47.5 mm |
| Swivel radius | 127 mm |
| Swivel interference | 254 mm |
| Dome diameter | 45.5 mm |

FITTING

| | |
|------------------------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 32 mm |
| Bolt length | 45 mm |
| Bolt thread position | 7 mm |
| Bolt mounting holes quantity | 2 |



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award

LINEA


5940UAP150R05-32 9002

EAN 4031582338898
Order number 00034522



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award